

# Digital Scanning Laser Vibrometer

# Scan-Series



#### HeNe Scanning Laser Vibrometer

Scanning Laser Doppler Vibrometry is an advanced measurement technique for the visualization of vibrations on the surface of nearly any object. Scanning Laser Vibrometer can measure and visualize vibration shapes and eigenmodes, capture the propagation of surface waves, validate FEM models, characterize vibration processes, and determine modal parameters.

## HIGHLIGHTS

- Excellent signal level
- Very compact
- Easy to operate
- Highest accuracy and resolution
- High-speed vibrations up to 10 m/s

#### IMAGING VIBRATION MEASUREMENT

The Scan-Series combine the superior signal quality of HeNe laser vibrometry with the informative value of imaging methods by scanning the object under test on a flexibly definable point grid. Different measurement surfaces, wider coverage, and measuring ranges are the key to new fields of application.

Scanning vibrometry makes it possible to test entire workpieces automatically in one measurement process without contact or any influence on the object. Thus, scanning vibrometry enables the capture of local resonances and global vibration modes with the lowest effort.

## Applications

#### Acoustics

- Automotive industry: Optimization of car door, automotive transmission, brakes, motor, NVH testing...
- Consumer market: Development of household appliance, electronic toothbrush, washing machine...
- Optimization of deflection shapes in loudspeaker, musical instruments...

#### Structrual Dynamics

- Automotive industry: Modal analysis, FE-model validation...
- Aviation and Aerospace industry: Airplane components, turbines...
- Material Research: non-destructive evaluation of material properties, material defect analysis...



#### **Example applications:**



Automotive industry



Material research & testing



Aerospace industry



Toolmaking and Mechanical Engineering



Electronics



MEMS



#### Set up

- Geometry definition
- Mesh generation / import
- Setup of the data acquisition / generator system



## **Automatic Scan**

- The whole grid is automatically scanned by the laser beam.
- making measurements at each grid point
- Time response and frequency response of each point and reference signals are displayed in real time during the scan.



## Visualization / Analysis

- 3D Animation to display your ODS
- (Operation deflection shape)
- Modal analysis
- Data export
- FEM model validation



## **Technical Data**

Measured Quantities – Performance Parameters							
Max. Frequency	Max. <sup>2</sup> Velocity	Best Vel. <sup>1</sup> Resolution	Max. <sup>2,3,4</sup> Displacement	Best Disp. <sup>1a</sup> Resolution	Max. <sup>2,3,4</sup> Acceleration	Best Accel. <sup>1</sup> Resolution	
25 MHz <sup>4</sup>	10 m/s	1.3 nm s <sup>-1</sup> /√ Hz	±50 mm	0.05 pm /√ Hz	32 Mg	1.8µg /√Hz	

General Measurement Specifications

Measured quantities	Velocity, displacement, acceleration
Frequency bandwidth <sup>2</sup>	0 Hz - 25 MHz <sup>4</sup>
Max. velocity <sup>2</sup>	10 m/s
Velocity measurement ranges <sup>2</sup>	14
Signal processing	Digital (FPGA based)
Source impedance	50 Ohm
Analog signal output	5× BNC, ±2 V (or ±10 V on request):
	- Velocity, displacement <sup>3</sup> , acceleration <sup>3</sup> , signal generator
	- Data rate: 160 MSamples/s @ 16-bit
External Trigger	Digital external trigger in/out via SMB
Filter	High-pass filter*: off / 10 / 20 / 40 / 80 / 160 / 320 / 640 Hz
	1.28 / 2.56 / 5 / 10 / 20 / 40 / 80 / 160 kHz
	Low-pass filter: off / 2.5 / 5 / 10 / 20 / 50 / 100 kHz
	Tracking filter: off / slow / fast
Integrated signal generator	<ul> <li>1 x signal generator (optional 2 x, 3 x, 4 x, 5 x)</li> <li>Preset standard and user-defined signal forms (sine, chirp, gaussian,)</li> <li>Import of arbitrary functions as text or audio wave-files</li> </ul>
Measurement Specifications – S	Scanning Operation Mode
Scan angle	50° × 40°, resolution < 0.001°, stability < 0.001°/ h
Max. scan points/s	> 50
Scan point density	Up to 512 × 512 scan points
Camera & Camera PC-Interface	CCD-Picture capture & live display: Full HD 1080p, 30x optical zoom, hori- zontal viewing angle: 63.7°(wide end) to 2.3°(tele end), USB 3.0
Digital Signal Output &	1 Gbit RJ45 Ethernet:
PC-Interface	- Digital data acquisition- and analysis software <i>OptoSCAN<sup>5</sup></i>
	- Digital remote control of device settings
BNC analog inputs	Measurement input, 2 x reference input (optional 4 x, 6 x, 8 x)
	24-bit A/D converter per channel
	support for IEPE (Integrated Electronic Piezoelectric) inputs
Sample size	From < 1 mm <sup>2</sup> up to several m <sup>2</sup>

<sup>&</sup>lt;sup>1</sup> The Resolution is defined as the signal amplitude (rms) corresponding to a signal-to-noise ratio (SNR) of OdB with 1 Hz spectral resolution at 50 % f<sub>max</sub> of smallest measurement range.

\* With displacement decoder

<sup>&</sup>lt;sup>1a</sup> The Resolution is defined as the signal amplitude (rms) corresponding to a signal-to-noise ratio (SNR) of OdB with 1 Hz spectral resolution.

<sup>&</sup>lt;sup>2</sup> Actual specifications depend on the configured decoder.

<sup>&</sup>lt;sup>3</sup> Optionally available

 $<sup>^{4}</sup>$  f > 100 kHz using internal signal generator. fmax: 10 – 25 MHz, vmax = 0.5 m/s

<sup>&</sup>lt;sup>5</sup> Standard included: Detailed program features listed below.

#### Measurement Specifications – Single-Point Operation Mode

Measuring ranges <sup>2</sup>	14 (velocity), 19 (displacement), 14 (acceleration)
Digital Signal Output &	1 Gbit RJ45 Ethernet:
PC-Interface	- Data rate: 1 GBit/s (max. 80 Msample/s, up to 32-bit)
	- Digital data acquisition- and analysis software <i>OptoGUI<sup>5</sup></i>
	- Digital remote control of device settings

## **Optical Specifications**

Working distances	50 mm 100 m
Laser wavelength	632.8 nm
Laser safety class	Output power < 1 mW, class 2
Lens	LR, focal length: 100 mm
Focusing	Auto-, remote-, and manual focussing

#### **General Device Specifications**

User interface output	Color screen 3.5" + 20 segment LED bargraph
User interface input	Touch screen, knobs with push-button, key switch (power)
Operating temperature	0 to 40°C
Storage temperature	-10°C to 65°C
Relative Humidity	max. 80%, non-condensing
Dimensions	Length × width × height (excluding handle): 450 x 224 x 180 mm
Weight	12 kg
Power supply	100 - 240 V AC (50-60Hz) or 12 V DC, 60 W (typical)
Portable Operation	Possible
Portable power supply	12 V DC portable charger <sup>3</sup>
Calibration interval	Every 24 month (recommended)





## Model Options - Decoders<sup>6,7</sup>

Model (Decoder) <sup>6,7</sup>	Description	Measuring Ranges <sup>6</sup>	Max. Velocity	Frequency Bandwidth -Scan
Basis	Versatile model with high resolution <sup>9</sup>	8	2 m/s	0 Hz – 100 kHz
Sense	Smallest measurement range ± 2.45 mm/s and highest resolution <sup>10</sup>	11	2 m/s	0 Hz – 1 MHz <sup>4</sup>
High Speed	Supports measurements up to highest ve- locities	11	10 m/s	0 Hz – 2.5 MHz <sup>4</sup>
HF	Supports measurements up to highest fre- quencies	9	5 m/s	0 Hz – 10 MHz <sup>4</sup>
Master	The all-rounder: Includes all Sense, High Speed, and High Frequency features	14	10 m/s	0 Hz – 10 MHz <sup>4</sup>
Master+	Enables measurements with highest frequencies	14	10 m/s	0 Hz – 25 MHz <sup>4</sup>

Overview Model Options and Characteristics of the standard included Scanning Decoder<sup>6,7</sup>

<sup>6</sup> For details see decoder data-sheets. <sup>7</sup> Variations from displayed models available on request.

<sup>8</sup> Exact measuring ranges listed in the identically named single-point velocity decoder data-sheets (D-VD-1, ...-2, ...-3, ...-4, ...-5, ...-5-25) <sup>9</sup> Best velocity resolution: 6 nm s  $^{-1}/\sqrt{Hz}$ <sup>10</sup> Best velocity resolution: 1.3 nm s<sup>-1</sup>/ $\sqrt{Hz}$ 

Decoder <sup>6,7</sup>		Measuring Ranges <sup>6</sup>	Smallest Range <sup>11,12,13</sup>	Largest Range	Frequency Bandwidth
D-VD-1	S	8	± 10 mm/s	± 2 m/s	0 Hz – 500 kHz
-DD-1	0	19	± 50 nm	± 50 mm	
-AD-1	0	8	± 160 g	± 0.64 Mg	
D-VD-2	S	11	± 1 mm/s	± 2 m/s	0 Hz – 1 MHz
-DD-2	0	19	± 50 nm	± 50 mm	
-AD-2	0	11	± 1.6 g	± 1.28 Mg	
D-VD-3	S	11	± 10 mm/s	± 10 m/s	0 Hz – 2.5 MHz
-DD-3	0	19	± 50 nm	± 50 mm	
-AD-3	0	11	± 160 g	± 16 Mg	
D-VD-4 -DD-4 -AD-4	S 0 0	9 19 9	± 10 mm/s ± 50 nm ± 160 g	± 5 m/s ± 50 mm ± 32 Mg	0 Hz – 10 MHz – 25 MHz <sup>3</sup>
D-VD-5	S	14	± 1 mm/s	± 10 m/s	0 Hz – 10 MHz
-DD-5	0	19	± 5 0 nm	± 50 mm	
-AD-5	0	14	± 1.6 g	± 32Mg	
D-VD-5-25	S	14	± 1 mm/s	± 10 m/s	0 Hz – 25 MHz <sup>14</sup>
-DD-5-25	0	19	± 50 nm	± 50 mm	
-AD-5-25	0	14	± 1.6 g	± 32Mg	

#### Characteristics of the Decoders for Single-Point Operation Mode<sup>6,7</sup>

S: Standard included O: Optional included

 $^{13}$  Best acceleration resolution: 1.8  $\mu$ g/vHz  $^{14}$  Velocity limited to 0.5 m/s at frequencies above 10 MHz

## Software





OptoGUI – Measurement & Analysis Software for data acquisition, analysis, and remote control when using the single-point operation mode. Live animation of measured time and frequency data.

OptoSCAN – Measurement & Analysis Software for data acquisition, analysis, and remote control in scanning operation mode. Animation of measured time data, various analysis functions, and the frequency response function of the scanned surface.

#### **OptoGUI software includes**

Remote control	Remotely control all vibrometer settings via ethernet.	S
Read-out	Read out data via ethernet with up to 80 MS/s	S
Time data	Live animation of measured vel. / disp. / accel. data	S
Export data	Export time data as .csv, .h5, .wav or .mat files	S
Fourier-Transformation	-Real-Time Fast Fourier Transform -up to 536 Mio. FFT lines	S
Peak identification	Automatically identify signal peaks in the frequency spectrum	S
Spectrogram	Show a live Spectrogram of the FFTs of the ongoing measurements	S
Fourier boundaries	Limit live FFT-calculation to certain time ranges of the time data	S
Signal trigger	Trigger your measurement with the vel., disp., or accel. signal	S
External trigger	Trigger your measurement with an external TTL signal (3.3 V)	0
Multiple traces	Record and recall multiple traces of the vel./disp./accel. time data	S
Arbitrary signal generator	Import file formats: .csv ASCII- or .wav audio files	0
	Pre-defined signals: sine, rectangle, chirp, random,	

#### Laser product label

DO NOT STARE INTO BEAM Class 2 Laser Product

Laser CLASS 2: Visible, red laser beam,  $\lambda$ = 632.8 nm Output power: < 1 mW



0

#### **OptoSCAN software includes**

Remote control	Remotely control all vibrometer settings via ethernet	S
Software architecture	64-bit, multithreaded, fast-responsive software architecture	S
Offline analysis	Analysis of data in offline post-processing	S
Individual Scan Points	Freely chose measurement and individual point positions	S
Arbitrary signal generator	Import file formats: .csv ASCII- or .wav audio files	S
	Pre-defined signals: sin, rectangle, chirp, random,	
Camera	Live video stream to monitor the measurement progress	S
Frequency functions	Calculation of FRF, FFT, Auto-Spectrum, Cross-Spectrum, Coherence	S
ODS (operating deflection shape)	3D-animation of mode shapes at selected frequencies	S
Time analysis	Time representation, analysis and animation. Seamlessly switching be- tween frequency and time representation.	0
Heatmap of FRF ampli- tude/phase	2D-Heatmap of the amplitude and phase of the frequency response func- tion of the measured velocity, displacement or acceleration response	S
Heatmap of FFT amplitude	2D-Heatmap of the FFT of the measurement (vel./disp./accel.) channel and all reference channels	S
Heatmap of time data RMS	2D-Heatmap of the root mean square of the time data	S
Heatmap of coherence	2D-Heatmap of the coherence between measurement and reference channels	S
Speckle-Tracking & point- wise autofocus	High-speed autofocus and configurable speckle-tracking for automatic increase of measurement data quality	S
Modal analysis	Analyze dynamical properties of the scanned structure	0
UFF-Interface	Multithreaded export of ODS data, time data, all frequency functions and data of reference channels	S
Audio-file export	Export of time data as .wav audio-files	S
Video export	Export animations of time data (wave-propagation) and selected mode- shapes as high resolution video file	S
Record Video	Resolution: Full HD (1920 x 1080), HD (1280 x 720) Recording Setup: - Period: Predefined number of recorded periodes - Free: Free hand 3D scene recording - Tracking Shot: User predefined 3D scene point of views with camera panning	S
Data processing	Digital filtering, signal averaging, FFT windows (including rectangle, exponential, Hanning, etc.), real-time integral or differential, display phase, real, imaginary, frequency response function (FRF), etc.	S
FFT lines	Up to 536 Mio.	S
Export data as:	.uff, .hdf5, .mat, and .wav files	S

## Accessories

+

<sup>s</sup> Standard included, <sup>o</sup> Optional available

Transport Case	Stable and waterproof Peli case for safe storage and transport of vibrometer External dimensions (L x B x H): 62,5 x 49 x 35 cm	S
Coaxial Unit	Brings the measurement laser and the camera onto the same optical axis.	0
Close-up Unit	For measurements of small objects at the shortest distances of a few mm	0
Protection window	Protects the scanning unit against dust, wind and acoustic excitation at high sound pressure levels.	0
Tripod with fluid head	Precisely align your vibrometer with high quality tripods by Manfrotto	0
Transport Bag	Compact und light transport bag for outdoor-measurements	0
Ring Light	For illumination of small test objects. Requires Close-up Unit.	0

## Maintenance Specials

## Warranty

Warranty	12 months	S
Warranty extension	Extension of standard warranty to 24 months	0
Software Updates		
Software maintenance	Free software updates within warranty period	S
Extended maintenance	Additional extension of software updates by 12+ months	0
Hardware Maintenance		
Hardware Maintenance	Free hardware maintenance within warranty period	S
Extended maintenance	Additional extension of hardware maintenance by 12+ months	0
Recalibration & cleaning	Check, cleaning & realignment of optical parts, check of laser output power, perform factory calibration	0

+









Optomet GmbH | Pfungstaedter Strasse 92 64297 Darmstadt | Germany Phone +49(0)6151-38432-0 | sales@optomet.de www.optomet.com